

















How to read the table: Find your desired sample storage tube or sample storage rack and see which rack/tube, rack cover and cap is compatible.

Rack Type →	Loborack -96			Roborack -96			Comorack -96	Micronic 96-1		Micronic 96-Q1		Micronic 96-2		Micronic 96-3		Micronic 96-4		Micronic 96-5	
Tube Size ↓																			
Cover Type →	High	Standard	Low	High	Standard	Low	Standard	High	Low	High	Low	High	Low	High	Low	High	Low	High	Low
0.30ml External Thread									Screw Cap + Push Cap										
0.40ml External Thread								Screw Cap + Push Cap											
0.50ml Internal Thread		Screw Cap	Push Cap*						Push Cap*	Screw Cap	Push Cap*								
0.75ml Internal Thread	Screw Cap	Push Cap*										Screw Cap	Push Cap*						
0.75ml External Thread (Hybrid)												Screw Cap + Push Cap							
0.80ml External Thread																	Screw Cap + Push Cap		
1.10ml Internal Thread					Screw Cap	Push Cap*									Screw Cap	Push Cap*			
1.10ml External Thread															Screw Cap + Push Cap				
1.40ml Round Bottom (No Thread)						Push Cap		Push Cap										Push Cap	
1.40ml Internal Thread				Screw Cap	Push Cap*		Push Cap									Screw Cap	Push Cap*		
1.40ml External Thread (Hybrid)																Screw Cap + Push Cap			
2.00ml Internal Thread																		Screw Cap	Push Cap*
2.00ml External Thread																		Screw Cap + Push Cap	
2.50ml Round Bottom (No Thread)**					Push Cap														

\*Or Low Profile Screw Cap.

\*\* For the 2.50ml Round Bottom Tube the Rack Cover is Extra High.

How to read the table: Find your desired sample storage tube or sample storage rack and see which rack/tube, rack cover and cap is compatible.

Rack type →	Micronic 48-1	Micronic 48-2	Micronic 48-3	Micronic 48-4	Micronic 24-1		Micronic 24-2	Micronic 24-4
Tube size ↓								
Cover	Low	High	High	High	High	Low	High	High
1.00ml external thread	Screw Cap							
1.50ml external thread hybrid						Screw Cap		
2.00ml external thread hybrid		Screw Cap						
3.00ml external thread hybrid 48-well			Screw Cap					
3.00ml external thread hybrid 24-well					Screw Cap			
3.50ml external thread							Screw Cap	
4.00ml internal thread				Screw Cap				
4.00ml external thread				Screw Cap				
6.00ml internal thread								Screw Cap
6.00ml external thread hybrid								Screw Cap

